

Rittal – The System.

Faster – better – everywhere.



SZ 2411.601

Cable gland, polyamide

State: 4/09/2025 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.601 - Cable gland, polyamide

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

Features

Model No.	SZ 2411.601
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Polyamide 6 Seal: CR/NBR
Colour	RAL 7035
IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Dimensions	Height: 22 mm
Thread	M12 x 1.5
Thread length	8 mm
Min. cable diameter	3 mm
Max. cable diameter	6.5 mm
Operating temperature range	-30 °C...100 °C
torque	1.8 Nm
Width across flats	15 mm
Dimensions	Thread: M12 x 1.5 Thread length: 8 mm
Type rating to UL 50E	Type 4X
Packs of	50 pc(s).
Net weight	0.05
Gross weight	0.22

Features

Customs tariff number	39269097
EAN	4028177810013
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

Approvals

Approvals	CSA + CSAus UR + C-UR (recognized) VDE
Explanations	Declaration of conformity Declaration of conformity UK