

Rittal – The System.

Faster – better – everywhere.



SK 3301.392

Air duct

State: 13/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3301.392 - Air duct for side air routing

For cold air supply to hubs with side air intake.

Features

| | |
|----------------------|---|
| Model No. | SK 3301.392 |
| Product description | Air duct, passive, for cold air intake to 482.6 mm (19") IT equipment with side air inlet. Suitable for use in conjunction with all-round partitioning around the mounting level via air baffle plates and targeted management of the airflow through the air duct. |
| Benefits | For superior air infeed to the rear 482.6 mm (19") equipment with side air routing Integral membrane cover allows cable entry to the rear Depth-variable |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 9005 |
| Supply includes | Air duct Adaptor for attaching to 482.6 mm (19") mounting angles Magnetic strip to cover the remaining vertical openings in the air baffle plate |
| Installation options | for TS IT 482.6 mm (19") mounting angles for TS IT 482.6 mm (19") mounting frames for 482.6 mm (19") mounting angles, standard |
| Assembly instruction | Only suitable for fitting on the front 482.6 mm (19") installation level Can only be mounted in the area of the vertical 19" openings of the air baffle plate |
| Dimensions | Height: 2 U |
| To fit | Enclosure type: TS IT VX IT Width: 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 1.55 kg |

Features

| | |
|-------------------------------|--|
| Gross weight | 1.8 kg |
| PCF per pack (cradle-to-gate) | 6.9 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC011217 |
| ETIM 8 | EC011217 |
| ECLASS 8.0 | 22410601 |
| Product description | SK Air duct, for side air flow, 2 U, depth-variable 275 - 418 mm, sheet steel, RAL 9005 |