

Rittal – The System.

Faster – better – everywhere.



SK 3114.200

**Digital enclosure internal
temperature display and thermostat**

State: 16/07/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3114.200 - Digital enclosure internal temperature display and thermostat

For installation in the enclosure door or wall.

Features

Model No.	SK 3114.200
Product description	For installation in the enclosure door or wall.
Technical specifications	Three-digit, 7-segment display Option of switching between °C/°F Includes 1800 mm long NTC sensor Two relay outputs as change-over contact and normally open contact (max. contact load 230 V, 6 A) Freely selectable switching difference
Colour	RAL 7035
Packs of	1 pc(s).
Operating temperature range	0 °C...50 °C
Setting range	5 °C...55 °C
Rated operating voltage	100 V - 230 V, 1~, 50 Hz/60 Hz 24 V - 60 V (DC)
Storage temperature range	-20 °C...70 °C
IP protection category to IEC 60529	IP 54
Net weight	0.258
Gross weight	0.259
Customs tariff number	90321020
EAN	4028177631434
ETIM 9	EC004587
ETIM 8	EC004587
ECLASS 8.0	27210707

Approvals

Approvals	UR
Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK