Rittal – The System.

Faster – better – everywhere.





SK 3311.490 Liquid Cooling Unit

State: 18/11/2025 (Source: rittal.com/nz-en)



SK 3311.490 - Liquid Cooling Unit LCU DX, single

Refrigerant-based enclosure cooling in single version for VX IT or Micro Data Center without heating up the installation room. With two output categories 3 kW and 6.5 kW, the ideal cooling solution for smaller IT applications.

Features

Model No.	SK 3311.490
Design	LCU DX 3 kW
Benefits	Space-saving solution by installing the internal unit in the VX IT
	server enclosure or the Micro Data Center
	Maximum energy efficiency due to EC fan technology and IT-based control
	Control of the server inlet temperature
	The inverter-controlled compressor adapts the cooling output to the current heat loss inside the enclosure
	Absorbed thermal energy is emitted directly to the ambient air at the
	(inverter-controlled) external unit's location, without heating up the installation room
Applications	Cooling unit for VX IT server racks and for Micro Data Centers
Function principle	The device supports front-to-back air routing typical of IT applications, and regulates the server inlet temperature to the set value
Material	Sheet steel, spray-finished
Colour	Internal unit: RAL 7035
	External unit: white
Supply includes	Internal unit (evaporator coil)
	External unit (inverter-controlled)
	482.6 mm (19") mounting trim panel with display and control
	components
	Condensate hose

© Rittal 2025 2

Features

Installation options in VX 482.6 mm (19") mounting angles, standard or dynamic, must be offset in the width by 50 mm off-centre The front distance between the 482.6 mm (19") mounting angles and the front edge of the VX frame must be at least 100 mm Two punched sections with mounting flanges are required for attachment on the inner mounting level Air baffle plates are required to separate the hot/cold zones within an enclosure A base/plinth is required to route the cable downwards Note Below the operating limit, fluctuations in the air inlet temperature are possible The electrical connection is made on the external unit. The internal unit is supplied by the external unit. IP protection category to IEC 60 External unit IP 20 External unit IP 20 External unit IP 3 kW Max. cooling output 3 kW Type of electrical connection Connection clamp Duty cycle 100 % Operating temperature The specified operating temperature refers to the external unit To fit Enclosure type: VX IT Width: = 800 mm Height: ≥ 1,800 mm Depth: ≥ 1,000 mm Internal unit dimensions Width: 105 mm Pepth: ≥ 300 mm Pepth: ≥ 300 mm Pepth: ≥ 300 mm Pepth: ≥ 300 mm Reted unit dimensions Width: 810 mm Height: 558 mm Pepth: 310 mm Rated operating voltage 230 V, 1~, 50 Hz Pre-fuse 16 A Rated current 7 A Packs of 1 pc(s).		
are possible The electrical connection is made on the external unit. The internal unit is supplied by the external unit. IP protection category to IEC 60 529 External unit IP 20 External unit IP X4 Modulation range 1 - 3 kW Max. cooling output 3 kW Type of electrical connection Connection clamp Duty cycle 100 % Operating temperature The specified operating temperature refers to the external unit To fit Enclosure type: VX IT Width: = 800 mm Height: ≥ 1,800 mm Depth: ≥ 1,000 mm Internal unit dimensions Width: 105 mm Height: 1,550 mm Depth: 820 mm External unit dimensions Width: 810 mm Height: 558 mm Depth: 310 mm Rated operating voltage 230 V, 1~, 50 Hz Pre-fuse 16 A Rated current 7 A	Installation options in VX	offset in the width by 50 mm off-centre The front distance between the 482.6 mm (19") mounting angles and the front edge of the VX frame must be at least 100 mm Two punched sections with mounting flanges are required for attachment on the inner mounting level Air baffle plates are required to separate the hot/cold zones within an enclosure
529 External unit IP X4 Modulation range 1 - 3 kW Max. cooling output 3 kW Type of electrical connection Connection clamp Duty cycle 100 % Operating temperature The specified operating temperature refers to the external unit To fit Enclosure type: VX IT Width: = 800 mm Height: ≥ 1,800 mm Depth: ≥ 1,800 mm Depth: ≥ 1,000 mm Internal unit dimensions Width: 105 mm Height: 1,550 mm Depth: 820 mm External unit dimensions Width: 810 mm Height: 558 mm Depth: 310 mm Rated operating voltage 230 V, 1~, 50 Hz Pre-fuse 16 A Rated current 7 A	Note	are possible The electrical connection is made on the external unit. The internal
Max. cooling output Type of electrical connection Connection clamp Duty cycle 100 % Operating temperature The specified operating temperature refers to the external unit To fit Enclosure type: VX IT Width: = 800 mm Height: ≥ 1,800 mm Depth: ≥ 1,000 mm Internal unit dimensions Width: 105 mm Height: 1,550 mm Depth: 820 mm External unit dimensions Width: 810 mm Height: 558 mm Depth: 310 mm Rated operating voltage 230 V, 1~, 50 Hz Pre-fuse 16 A Rated current 7 A	- •	
Type of electrical connection Duty cycle 100 % Operating temperature The specified operating temperature refers to the external unit To fit Enclosure type: VX IT Width: = 800 mm Height: ≥ 1,800 mm Depth: ≥ 1,000 mm Internal unit dimensions Width: 105 mm Height: 1,550 mm Depth: 820 mm External unit dimensions Width: 810 mm Height: 558 mm Depth: 310 mm Rated operating voltage 230 V, 1~, 50 Hz Pre-fuse 16 A Rated current 7 A	Modulation range	1 - 3 kW
Duty cycle 100 % Operating temperature The specified operating temperature refers to the external unit To fit Enclosure type: VX IT Width: = 800 mm Height: ≥ 1,800 mm Depth: ≥ 1,000 mm Internal unit dimensions Width: 105 mm Height: 1,550 mm Depth: 820 mm External unit dimensions Width: 810 mm Height: 558 mm Depth: 310 mm Rated operating voltage 230 V, 1~, 50 Hz Pre-fuse 16 A Rated current 7 A	Max. cooling output	3 kW
Operating temperature The specified operating temperature refers to the external unit To fit Enclosure type: VX IT Width: = 800 mm Height: ≥ 1,800 mm Depth: ≥ 1,000 mm Internal unit dimensions Width: 105 mm Height: 1,550 mm Depth: 820 mm External unit dimensions Width: 810 mm Height: 558 mm Depth: 310 mm Rated operating voltage 230 V, 1~, 50 Hz Pre-fuse 16 A Rated current 7 A	Type of electrical connection	Connection clamp
To fit Enclosure type: VX IT Width: = 800 mm Height: ≥ 1,800 mm Depth: ≥ 1,000 mm Internal unit dimensions Width: 105 mm Height: 1,550 mm Depth: 820 mm External unit dimensions Width: 810 mm Height: 558 mm Depth: 310 mm Rated operating voltage 230 V, 1~, 50 Hz Pre-fuse 16 A Rated current 7 A	Duty cycle	100 %
Width: = 800 mmHeight: ≥ 1,800 mmDepth: ≥ 1,000 mmInternal unit dimensionsWidth: 105 mmHeight: 1,550 mmDepth: 820 mmExternal unit dimensionsWidth: 810 mmHeight: 558 mmDepth: 310 mmRated operating voltage230 V, 1~, 50 HzPre-fuse16 ARated current7 A	Operating temperature	The specified operating temperature refers to the external unit
Height: 1,550 mm Depth: 820 mm External unit dimensions Width: 810 mm Height: 558 mm Depth: 310 mm Rated operating voltage 230 V, 1~, 50 Hz Pre-fuse 16 A Rated current 7 A	To fit	Width: = 800 mm Height: ≥ 1,800 mm
Height: 558 mm Depth: 310 mm Rated operating voltage 230 V, 1~, 50 Hz Pre-fuse 16 A Rated current 7 A	Internal unit dimensions	Height: 1,550 mm
Pre-fuse 16 A Rated current 7 A	External unit dimensions	Height: 558 mm
Rated current 7 A	Rated operating voltage	230 V, 1~, 50 Hz
	Pre-fuse	16 A
Packs of 1 pc(s).	Rated current	7 A
	Packs of	1 pc(s).

© Rittal 2025

3

Features

Net weight	95.475
Gross weight	100.5
Customs tariff number	84158200
EAN	4028177709348
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704

Approvals

Certificates	EAC
Explanations	Declaration of conformity

© Rittal 2025

Tender text

3311.490 LCU DX 3 kW

LCU DX, 3 kW split cooling unit consisting of an internal unit (evaporator) and an external unit (inverter controlled cooling unit).

The internal unit is designed so that it can be installed in a 800 mm wide VX IT server enclosure or in a Micro Data Centre.

It is constructed in IT-optimised design, so that the "front to back" air routing of the 19" components is ideally supported.

The preferred area of application is in small to medium-sized locations, in which the server racks are cooled directly - without cooling the entire room.

The LCU DX internal unit is mounted laterally in the server enclosure or in the Micro Data Centre and it forms a closed system with the latter. The internal unit of the LCU DX extracts the warm server exhaust air directly from the rear part of the enclosure and blows the cooled air laterally in front of the 19" level.

The enclosure of the internal unit consists of powder coated sheet steel in RAL 7035, in which a direct evaporator, two EC radial fans, condensate tray and condensate discharge are integrated.

The condensation discharge has to be provided on-site.

The devices are constructed in such a way that assembly can be carried out in the IT server rack on the left or right.

In addition, a microprocessor controller is placed in the internal unit. The reference variable that controls the device is the server air inlet temperature.

This can be set at between 17 and 30°C on the remote operating unit. The operating unit is installed in a 19" trim panel (3 U). This is mounted on the rear 19" level of the VX IT rack or of the Micro Data Centre.

The external sensor that belongs to the device is placed near the front of the server.

The external unit with the inverter-controlled compressor permits stepless power adjustment, even in partial-load operation (1-3 kW).

The connection between the internal unit and the external unit is made by means of copper piping, a data line and the power supply. The internal device is supplied with voltage by the external device. R410a is used as a refrigerant.

© Rittal 2025 5

The on-site installation and commissioning, the laying of refrigerant lines and the evacuation and filling of the system with refrigerant are not included in the range of goods and services supplied. This work must be performed by qualified personnel.

Technical specifications:

Useful cooling output 3 kW

Fans installed in the internal unit: 2

Reference variable: Server air inlet temperature pre-set at 22°C

Voltage supply: 230 V, 1~, N, PE, 50 Hz

Pre-fuse: 16 A Refrigerant: R410a Line length, max.: 30 m

Max. height difference (external unit): 12 m

Dimensions of the internal unit, W x H x D: $105 \times 1550 \times 820 \text{ mm}$ Dimensions of the external unit W x H x D: $810 \times 558 \times 310 \text{ mm}$

Weight of the internal unit: 48 kg Weight of the external unit: 38 kg

Ambient temperature range of the external unit: -20°C to +45°C

© Rittal 2025 6