

# Rittal – The System.

Faster – better – everywhere.



## SK 3182.125 Pleated filter

State: 13/07/2025 (Source: [rittal.com/nz-en](https://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3182.125 - Pleated filter for fan-and-filter units, roof-mounted fans, cooling units and chillers

The high-quality pleated filter technology permits a significant increase in the volumetric air flow compared to conventional chopped-fibre filter mats. Cooling unit performance is improved and energy consumption is lower. The enhanced filtration properties also mean less dust in the enclosure or unit, and the resulting longer maintenance intervals reduce service costs significantly.



## Features

Model No.	SK 3182.125
Design	for filter fans / outlet filters
Material	Pleated filter: Based on polyester, meltblown polycarbonate Absorber mat: 100% polyester
Colour	White
Note	Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
To fit Model No.	3240.3xx 3240.7xx 3240.900 3241.7xx 3241.900
Dimensions	Width: 212.5 mm Height: 212.5 mm Depth: 21 mm
Dimensions of absorber mat	Width: 221 mm Height: 221 mm

# Features

IP protection category to IEC 60529	IP 55 in fan-and-filter units/outlet filters
Note on Model No.	No suitable for use in EMC filter fans.
Packs of	5 pc(s).
Net weight	0.35
Gross weight	0.38
Customs tariff number	56039390
EAN	4028177969094
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

# Approvals

Approvals	UR + C-UR (recognized)
-----------	------------------------