Rittal - The System.

Faster - better - everywhere.





SK 3342.500

Rack-mounted fans for 482.6 mm (19")

State: 4/11/2025 (Source: rittal.com/nz-en)



SK 3342.500 - Rack-mounted fans for 482.6 mm (19") Air throughput 320 - 480 m³/h

Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.

Features

Model No.	SK 3342.500
Product description	Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.
Colour	RAL 7035
Supply includes	Fully wired unit ready for connection Terminal strip and assembly parts
Air throughput (unimpeded air flow)	480 m³/h
Note on Model No.	Rack-mounted fan for metric mounting angles available on request. Version with monitoring
Rated operating voltage	115 V - 230 V, 1~, 50 Hz/60 Hz 24 V (DC)
Rated current max.	At 50 Hz: 0.85 A
Pre-fuse	Miniature circuit-breaker/fuse: 6 A
Dimensions	Width: 482.6 mm Height: 44 mm Depth: 200 mm
Distance between axes of fans	105 mm
No. of fans	3
Noise level	With DC: 51 dB(A)
Operating temperature range	-10 °C55 °C
Packs of	1 pc(s).

© Rittal 2025 2

Features

Net weight	1.8
Gross weight	1.998
Customs tariff number	84145915
EAN	4028177041530
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Approvals	UR + C-UR (recognized) VDE
Explanations	Declaration of conformity

© Rittal 2025 3