## Rittal - The System.

Faster – better – everywhere.



# SK 3212.115 Air/water heat exchangers

State: 1/12/2025 (Source: rittal.com/nz-en)



## SK 3212.115 - Air/water heat exchangers wall-mounted

Output classes 375 – 5,000 W. For use in tough environments. Convenient mounting options and flexible water connection options. External mounting or full internal mounting possible.

#### **Features**

Model No.	SK 3212.115
Design	wall-mounted
	Water-carrying parts, copper/brass (Cu/CuZn)
Product description	For use in harsh environments and temperature ranges up to +70
	°C. User-friendly assembly plus flexible water connection options.
	External mounting or full internal mounting are supported.
Colour	RAL 7035
Supply includes	Fully wired ready for connection
	Drilling template
	Sealing and assembly parts
Total cooling output	L 35 W 10 at 200 l/h: 0.3 kW
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 26 W
	At 60 Hz: 30 W
Rated current max.	At 50 Hz: 0.23 A
	At 60 Hz: 0.24 A
Permissible operating pressure (p.	1 - 10 bar
max.)	
Duty cycle	100 %
Cooling medium	Water (see Internet for specifications)
Water inlet temperature	1 °C30 °C
Water connections	3%" connector sleeve
Operating temperature range	1 °C70 °C
Note	Integral non-return valve for version with e-Comfort controller

© Rittal 2025 2

## **Features**

Dimensions	Width: 150 mm
	Height: 300 mm
	Depth: 85 mm
	<u> </u>
Note on Model No.	Extended delivery times.
Pre-fuse	Miniature circuit-breaker/fuse: 2 A
Setting range	20 °C55 °C
Protection category to IEC 60 529	IP 55
Packs of	1 pc(s).
Net weight	3.1
Gross weight	3.16
Customs tariff number	84158300
EAN	4028177430945
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
EULAGO 0.0	27100712

## **Approvals**

Explanations Declaration of conformity

© Rittal 2025 3

#### Tender text

Wall-mounted air/water heat exchanger For use in tough environments. Flexible water connection options.

Total cooling output L 35 W 10, 200l/h: 0.3 kW Rated operating voltage: 115 V, 50/60 Hz Refrigerant: Water (see specifications)

Water-carrying parts: Cu/CuZn

Dimensions [W x H x D]: 150 x 300 x 85 mm Ambient temperature range: 1°C to 70°C Water inlet temperature range: 1°C to 30°C Type of connection: Plug-in terminal strip Protection category to IEC 60 529: IP 55

Weight: 3.2 kg Colour: RAL 7035

© Rittal 2025 4