

Rittal – The System.

Faster – better – everywhere.



SK 3215.700

Air/water heat exchangers

State: 9/04/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3215.700 - Air/water heat exchangers wall-mounted HD

Air/water heat exchanger for hygiene-critical production zones in the food and beverage industry – the optimum addition to the Rittal Hygienic Design range. The cleaning-friendly design reduces the risk of contamination and ensures food safety.



Features

| | |
|---------------------|--|
| Model No. | SK 3215.700 |
| Design | Water-carrying parts, copper/brass (Cu/CuZn) |
| Product description | Air/water heat exchanger for hygiene-critical production zones in the food and beverage industry – the optimum addition to the Rittal Hygienic Design range. The cleaning-friendly design reduces the risk of contamination and ensures food safety. |
| Benefits | Easy-to-clean, hygienic design A roof tilt of 30° prevents objects from being deposited on it, and allows liquids to run off quickly All-round external, replaceable silicone seal prevents the accumulation of dirt between the enclosure and the air-water heat exchanger. |
| Material | Enclosure: Stainless steel 1.4301 (AISI 304) |
| Surface finish | Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm |
| Supply includes | Fully wired ready for connection Drilling template Sealing and assembly parts |

Features

| | |
|--|--|
| Total cooling output | L 35 W 10 at 200 l/h: 1 kW L 35 W 10 at 400 l/h: 1.2 kW |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Power consumption Pel | At 50 Hz: 77 W At 60 Hz: 104 W |
| Rated current max. | At 50 Hz: 0.38 A At 60 Hz: 0.47 A |
| Permissible operating pressure (p. max.) | 1 - 10 bar |
| Duty cycle | 100 % |
| Cooling medium | Water (see Internet for specifications) |
| Water inlet temperature | 1 °C...30 °C |
| Water connections | G 3/8" external thread |
| Temperature control | Thermostat-controlled magnetic valve |
| Temperature monitoring | Internal thermostat, with change-over contact, switching load 16 A, setting range +20 °C ... +60 °C (factory setting +35 °C) |
| Operating temperature range | 1 °C...70 °C |
| Dimensions | Width: 215 mm Height: 982 mm Depth: 100 mm |
| Pre-fuse | Miniature circuit-breaker/fuse: 4 A |
| Setting range | 20 °C...60 °C |
| Protection category to IEC 60 529 | IP 56/59 |
| Protection category NEMA | NEMA 4X |
| Packs of | 1 pc(s). |
| Net weight | 14 kg |
| Gross weight | 14 kg |
| Customs tariff number | 84158300 |
| ETIM 9 | EC002515 |

Features

| | |
|---------------------|---|
| ETIM 8 | EC002515 |
| ECLASS 8.0 | 27180712 |
| Product description | SK Air/water heat exchanger, wall-mounted, HD, 1.2 kW, 230 V, 1~, 50/60 Hz, Thermostat-controlled magnetic valve, WHD: 215 x 982 x 100 mm |

Approvals

| | |
|--------------|---|
| Approvals | CSA UL + C-UL - FTFA UR + C-UR (recognized) |
| Explanations | Declaration of conformity |

Tender text

Air/water heat exchangers wall-mounted HD

Air/water heat exchanger for hygienically sensitive production zones in the food and consumables

industry – the optimum addition to the Rittal Hygienic Design range. The cleaning-friendly design

reduces the risk of contamination and ensures food safety.

Total cooling output L 35 W 10, 200l/h: 1 kW

Total cooling output L 35 W 10, 400l/h: 1,2 kW

Rated operating voltage: 230 V, 1~, 50 Hz/60 Hz

Dimensions WxHxD [mm]: 215x982x100

Material (Enclosure): Stainless steel 1.4301 (AISI 304)

Surface finish (Enclosure): Brushed, grain 400, peak-to-valley height < 0,8 µm

Cooling medium: Water (see instructions for specifications)

Water-carrying parts: Cu/CuZn

Water connections: G 3/8" AG

Permissible operating pressure (p. max.): 1 bar to 10 bar

Temperature control operation (environment): +1°C to +70°C

Temperature control water inlet: +1°C to +30°C

Setting range: +20°C bis +60°C

Temperature monitoring: Internal thermostat, with change-over contact, switching load 16 A, setting

range +20°C ... +60°C (factory setting +35°C)

Temperature control: Thermostat-controlled magnetic valve

Type of connection: Plug-in terminal strip

Miniature circuit-breaker/fuse: 4 A

Power consumption Pel: 77/104 W

Rated current (max.): 0,38/0,47 A

Protection category IP to IEC 60 529: IP 56/59

Protection category NEMA: 4X

Weight: 14 kg