Rittal – The System.

Faster – better – everywhere.





SK 3237.724 Blue e+ filter fan


State: 1/11/2025 (Source: rittal.com/nz-en)



SK 3237.724 - Blue e+ filter fan

Complete fan-and-filter units for tool-free installation in surfaces. Air throughput $20-1,160\,\text{m}^3/\text{h}$, protection category IP 54 as standard.







Features

Model No.	SK 3237.724	
Design	wall-mounted	
Product description	Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure.	
Benefits	Easy filter changes, thanks to a new opening mechanism on the louvred grille Faster installation on the enclosure with optimised detent hooks Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability Tool-free assembly	
Material	Plastic	
Colour	RAL 7035	
Supply includes	Complete unit ready to install, including chopped-fibre filter mat	
Fan	Axial, DC motor	
Air throughput, unimpeded airflow (with chopped-fibre filter)	With DC: 20 m³/h	

© Rittal 2025

Features

Air throughput with matching outlet filter including chopped-fibre filter	With DC: 15 m³/h	
Rated operating voltage	24 V (DC)	
Power consumption Pel	With DC: 1.4 W	
Rated current max.	With DC: 0.06 A	
Dimensions	Width: 116.5 mm Height: 116.5 mm Depth: 64.5 mm	
Installation depth	46 mm	
Mounting cut-out	Cut-out width: 92 mm Cut-out height: 92 mm	
IP protection category to IEC 60 529	IP 54 with chopped-fibre filter IP 56 with chopped-fibre filter and hose-proof hood	
Protection category NEMA	Type 12 with chopped-fibre filter Type 3, 3R with chopped-fibre filter and hose-proof hood	
Pre-fuse	Miniature circuit-breaker/fuse: 2 A	
Note	With the filter fan 3237.XXX, electrical connection is made via two single wires (length approx. 300 mm) on the unit, for all other filter fans, a screwless spring terminal is used	
Operating temperature range	-15 °C55 °C	
Storage temperature range	-30 °C70 °C	
Noise level	With DC: 42 dB(A)	
Packs of	1 pc(s).	
Net weight	0.21	
Gross weight	0.292	
Customs tariff number	84145915	
EAN	4028177998278	
ETIM 9	EC000320	
ETIM 8	EC000320	

© Rittal 2025 3

Features

CLASS 8.0	27180716

Approvals

Approvals	30 - KC Korea
	UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025