


Rittal – The System.

Faster – better – everywhere.



DK 5301.652

Sheet steel door, vertically divided, vented

State: 16/04/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5301.652 - Sheet steel door, vertically divided, vented for VX IT

To replace existing doors. The vented surface area is approx. 85% perforated.



Features

Model No.	DK 5301.652
Product description	To replace existing doors. The vented surface area is approx. 85% perforated.
Material	Sheet steel
Surface finish	Spray-finished
Colour	Door: RAL 7035 Comfort handle VX, hinges: RAL 9005
Supply includes	Door, vertically divided, with comfort handle VX for semi-cylinders with security lock 3524 E, right 3 x 180° hinges, fitted on each half of the door Assembly parts
Assembly instruction	For a door opening angle of 180° when baying, a 180° baying hinge is required
Note	Door opening angle for stand-alone siting: max. 240° Door opening angle when baying: max. 160°

Features

IP protection category to IEC 60529	IP 20
To fit	Enclosure type: VX IT Width: 800 mm Height: 2,000 mm
Packs of	1 pc(s).
Net weight	15 kg
Gross weight	15.8 kg
Customs tariff number	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204
Product description	Sheet steel door, vertically divided, vented for VX IT, to replace existing doors. The vented surface area is approx. 85% perforated. For enclosure width: 800 mm, for enclosure height: 2,000 mm