

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.454

## Crimping machine R8 E

State: 5/02/2026 (Source: [ittal.com/nz-en](http://ittal.com/nz-en))



FRIEDHELM LOH GROUP

# AS 4050.454 - Crimping machine R8 E

Electrically driven wire stripping and crimping machine for taped wire end ferrules on a reel.



## Features

Model No.	AS 4050.454
Design	Touchscreen display
Product description	Electrically powered wire stripping and crimping machine for taped wire end ferrules on a reel.
Benefits	<ul style="list-style-type: none"><li>Easy to operate</li><li>Fast adjustment</li><li>Flexible use in the workshop</li><li>Rapid replacement of consumables</li></ul>
Technical specifications	<ul style="list-style-type: none"><li>Crimping range 0.5 - 2.5 mm<sup>2</sup> (AWG 20 - 14)</li><li>Crimping length 8 mm (0.31 in.)</li><li>Insertion length 40 mm (1.57 in.)</li></ul>
Note	The standard crimping form is trapezoid – others available on request
Dimensions	<ul style="list-style-type: none"><li>Width: 288 mm</li><li>Height: 230 mm</li><li>Depth: 345 mm</li></ul>
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	100 VA
Compression	Trapezoid crimp
Cycle time	1.8 s
Packs of	1 pc(s).

# Features

---

Net weight	16
Gross weight	16
Customs tariff number	84798997
EAN	4028177813465
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890

---