

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.456 Crimping machine RC

State: 15/12/2025 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.456 - Crimping machine RC

Electropneumatic crimping machine with 5-way magazine for processing insulated wire end ferrules in various cross-sections on a reel.

## Features

Model No.	AS 4050.456
Design	Touchscreen display Select the wire cross-section via touchscreen Support may be fitted with a maximum of 23,000 wire end ferrules
Product description	
Benefits	Easy to operate Secure, fast processing of insulated wire end ferrules No set-up time, thanks to automatic tool change Simple, quick component mounting No changing of the wire end ferrules required due to 5-way magazine
Technical specifications	Crimping range 0.5 - 2.5 mm <sup>2</sup> (AWG 20 - 14) Crimping length 8 and 10 mm Insertion length 27 mm (1.06 in.)
Note	The standard crimping form is trapezoid – others available on request
Dimensions	Width: 335 mm Height: 565 mm Depth: 485 mm
Compressed air connection	5.5 bar
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	16 VA
Compression	Trapezoid crimp
Cycle time	2 s
Packs of	1 pc(s).

# Features

Net weight	24.8
Gross weight	25.4
Customs tariff number	84624900
EAN	4028177930865
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	17130101