Rittal - The System.

Faster – better – everywhere.





AS 4055.070 Manual hydraulic punch set, M16 -M63

State: 3/11/2025 (Source: rittal.com/nz-en)



AS 4055.070 - Manual hydraulic punch set, M16 - M63

Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.

Features

Model No.	AS 4055.070
Design	This set includes the standard hole punches M16 to M63
Product description	Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.
Benefits	Extend tool life with a built-in overpressure valve
	Hole punches, hydraulic punches and accessories for making round square and rectangular cut-outs in steel steel and stainless steel
Supply includes	Manual hydraulic punch, straight
	7 splitter hole punches, triple splitting
	Hydraulic screw Ø 19 mm
	Hydraulic screw Ø 9.5 / 19 mm
	HSS pilot drill Ø 10 mm
	Spacer sleeve set (3-part)
	Plastic case
Machinable material	Sheet steel
Maximum machinable material	2 mm
thickness, sheet steel	2 mm
	2 mm
	3 mm
Ø punch	16.2 mm
	20.4 mm
	25.4 mm
	32.5 mm
	40.5 mm
	50.5 mm
	63.5 mm

© Rittal 2025

Features

For threads	M16
	M20
	M25
	M32
	M40
	M50
	M63
Packs of	1 pc(s).
Net weight	5.3
Gross weight	5.34
Customs tariff number	82034000
EAN	4028177807945
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049046

© Rittal 2025 3