Rittal – The System.

Faster – better – everywhere.







AS 4055.237 Hole punch, round

State: 9/11/2025 (Source: rittal.com/nz-en)



AS 4055.237 - Hole punch, round for sheet steel

For punching round cut-outs

Features

Model No.	AS 4055.237
Design	With 3 cutting points
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Female dies Male dies Tension screw without ball bearing
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	3 mm
Ø punch	37 mm
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 55 mm
Hydraulic tension screw Ø	19 mm
Packs of	1 pc(s).
Net weight	0.453
Gross weight	0.487
Customs tariff number	82073010
EAN	4028177808294
ETIM 9	EC000156
ETIM 8	EC000156

© Rittal 2025

Features

ECLASS 8.0

21049047

© Rittal 2025 3