
Rittal – The System.

Faster – better – everywhere.



DK 7064.000
Telescopic slides

State: 22/11/2026 (Source: www.rittal.com/nz-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7064.000 - Telescopic slides for component shelves, for mounting on the VX enclosure frame and for upgrading existing VX and TS applications

For retrospectively converting fixed component shelves to full withdrawal by exchanging the fastening bolts or mounting rails (heavy-duty version) for the telescopic slides.

Features

Model No.	DK 7064.000
Product description	Fixed component shelves are easily converted to full withdrawal. For this purpose, the existing fastening bolts or mounting rails (heavy-duty version) are exchanged for the telescopic slides.
Material	Sheet steel
Surface finish	Zinc-plated
Suitable for component shelf depth	400 mm
Load capacity	100 kg
Note	For installation and locking on a 25 mm pitch pattern in the enclosure depth.
Packs of	2 pc(s).
Net weight	2.24 kg
Gross weight	2.44 kg
PCF per pack (cradle-to-gate)	9.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Telescopic slides for component shelf, 100 kg, For D: 400 mm

Tender text

Telescopic slides for 400 mm deep component shelves
Version: max. load capacity 100 kg
The telescopic slides are installed between the installation kit and a 400 mm deep component shelf. The telescopic slides have a maximum load capacity of 50 kg and are lockable in two positions.
Material: sheet steel, zinc-plated
For component shelf depth: 400 mm

© Rittal 2026