

Rittal – The System.

Faster – better – everywhere.



VX 5301.348

Gland plate module for side cable entry

State: 3/08/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.348 - Gland plate module for side cable entry for VX IT

With adjustable openings and brush strips on both sides. The version which is open at the side even allows retrospective fitting of the base plate module with the cables already installed.

Features

Model No.	VX 5301.348
Design	Version for cable entry with rubber cable clamp strip at the sides:
Product description	With adjustable opening and brush strips on both sides. The version which is open at the side even allows the base plate module to be retro-fitted with the cables already installed.
Material	Module plate: Sheet steel Brush strip: Plastic, UL 94 HB, halogen-free
Surface finish	Module plate: Zinc-plated
Supply includes	Assembly parts
Assembly instruction	Several gland module plates must be combined to seal the base completely in the VX IT The gland plate module may be combined in exchange with other base modules with a depth of 237.5 mm.
Note	Gland plate modules with brush strip not suitable for applications with a protection category to IEC 60 529
To fit	Enclosure type: VX IT Width: = 800 mm
Packs of	1 pc(s).
Net weight	2
Gross weight	2.36
PCF per pack (cradle-to-gate)	9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098

Features

EAN	4028177951006
ETIM 9	EC002620
ECLASS 8.0	27189261