


Rittal – The System.

Faster – better – everywhere.



VX 5301.518

Castor module

State: 14/01/2026 (Source: rittal.com/nz-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 5301.518 - Castor module for VX, VX IT

For easy movement directly at the point of use, even with fully configured enclosures.

Features

| | |
|-----------------------|--|
| Model No. | VX 5301.518 |
| Product description | For mobile use even with preconfigured enclosures. The castor module is screw-fastened to the structure directly underneath the base frame and is suitable for transporting configured enclosures on flat ground and inside buildings. |
| Supply includes | 1 transport module with 2 castors 1 transport module with 2 castors, fixed Assembly parts |
| Dimensions | Width: 756 mm Height: 203 mm Depth: 79 mm |
| Assembly instruction | The base area must be open at the mounting points |
| To fit | Enclosure type: VX: = 800 mm Enclosure type: VX IT |
| Load capacity | Max. admissible load: Static 15,000 N Max. admissible load: Dynamic 10,000 N |
| Note | The maximum admissible load capacity (dynamic) of 10,000 N refers to rolling over flat ground. |
| Packs of | 1 pc(s). |
| Net weight | 11.5 |
| Gross weight | 12.12 |
| Customs tariff number | 94039910 |
| EAN | 4028177952515 |
| E-Number Sweden | E7282571 |
| ETIM 9 | EC002621 |
| ECLASS 8.0 | 27189262 |

Tender text

Castor module for W: 800 mm

For easy movement on site, can be mounted directly on the IT rack.

Scope of delivery:

1 transport module with 2 castors

1 transport module with 2 baying clamps, fixed

Assembly parts