

Rittal – The System.

Faster – better – everywhere.



VX 5301.518

Castor module

State: 23/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.518 - Castor module for VX, VX IT

For easy movement directly at the point of use, even with fully configured enclosures.

Features

Model No.	VX 5301.518
Supply includes	1 transport module with 2 castors 1 transport module with 2 castors, fixed Assembly parts
Dimensions	Width: 756 mm Height: 82.5 mm Depth: 79 mm
Assembly instruction	The base area must be open at the mounting points
To fit	Enclosure type: VX: = 800 mm Enclosure type: VX IT
Load capacity	Max. admissible load: Static 15,000 N Max. admissible load: Dynamic 10,000 N
Note	The maximum admissible load capacity (dynamic) of 10,000 N refers to rolling over flat ground.
Packs of	1 pc(s).
Net weight	11.5 kg
Gross weight	12.12 kg
Customs tariff number	94039910
ETIM 9	EC002621
ECLASS 8.0	27189262
Product description	Castor module for VX IT, for W: 800 mm, for easy movement directly at the point of use, for mounting directly on the enclosure.

Tender text

Castor module for W: 800 mm

For easy movement on site, can be mounted directly on the IT rack.

Scope of delivery:

1 transport module with 2 castors

1 transport module with 2 baying clamps, fixed

Assembly parts