

Rittal – The System.

Faster – better – everywhere.



DK 7170.535

Fibre-optic splicing box with telescopic pull-out

State: 6/08/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7170.535 - Fibre-optic splicing box with telescopic pull-out lockable

To accommodate splicing cassettes, optimum access thanks to telescopic pull-out.

Features

Model No.	DK 7170.535
Product description	The 482.6 mm (19") splicing box is designed to accommodate splicing cassettes and can be installed in any network distributor with 482.6 mm (19") accommodation and used as a fibre-optic termination or distributor. The rear section of the splicing box is completely open for cable entry, a rubber cable clamp strip provides protection against dust. The fibre-optic cables can be secured with cable ties or cable clamps, two strain relief clips and cable routing clips for the fibre stock provide a solution to suit any fibre-optic wiring system.
Benefits	<p>The telescopic pull-out provides optimum access to the splicing cassettes and cable clamp</p> <p>The variable cassette fixture permits twist-proof installation of all standard splicing cassettes</p> <p>The security lock fitted at the front protects against unauthorised access</p>
Material	Sheet steel
Colour	RAL 7035
Supply includes	<p>Splicing box</p> <p>Cable routing clips</p> <p>Security lock</p> <p>Cassette cover</p> <p>Mounting accessories for patch panel</p>
Number of splicing cassettes max	2
Note	Supplied without patch panels and splicing cassettes
Installation depth	363 mm
Units	1 U

Features

Packs of	1 pc(s).
Net weight	5.584
Gross weight	5.88
Customs tariff number	94032080
EAN	4028177166769
ETIM 9	EC001129
ECLASS 8.0	19170113

Tender text

Fibre-optic splicing box for 482.6 mm (19")
installation, 1 U

The 482.6 mm (19") splicing box is designed to accommodate splicing cassettes and can be installed in any network distributor with 482.6 mm (19") accommodation and used as a fibre-optic termination or distributor. The telescopic pull-out provides optimum access to the splicing cassettes and cable clamp. The variable cassette fixture permits twist-proof installation of all standard splicing cassettes. The security lock fitted at the front protects against unauthorised access. The rear section of the splicing box is completely open for cable entry; a rubber cable clamp strip provides protection against dust. The fibre-optic cables can be secured with cable ties or cable clamps; two strain relief clips and cable routing clips for the fibre stock provide a solution to suit any fibre-optic wiring system.

Version: sheet steel

Paint finish: RAL 7035.