

Rittal – The System.

Faster – better – everywhere.



DK 7824.380

Sheet steel door, vertically divided, vented

State: 23/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7824.380 - Sheet steel door, vertically divided, vented for DK-TS

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

Features

| | |
|-------------------------------------|---|
| Model No. | DK 7824.380 |
| Product description | With 130° hinges and locking rod, including comfort handle for profile half-cylinders with security lock no. 3524 E. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced. The extensive door perforations additionally support climate control of the installed equipment. Perforated surface with air inlet openings > 78%. |
| Material | Sheet steel |
| Supply includes | Assembly parts |
| IP protection category to IEC 60529 | IP 20 |
| To fit | Enclosure type: DK-TS Width: 800 mm Height: 2,000 mm |
| Packs of | 1 pc(s). |
| Net weight | 26.32 kg |
| Gross weight | 28 kg |
| Customs tariff number | 94039910 |
| ECLASS 8.0 | 27182204 |

Tender text

TS vertically divided vented sheet steel door

Vertically divided 1.5 mm sheet steel door with extensive door perforations and vertical locking rod fitted in the centre, comfort handle with 3524 E security lock fitted as standard item, ensures optimum ventilation as well as an access protected design. A semi-cylinder can also be fitted (40/45 mm) as per DIN 18254.

135° door opening angle. The reduced swivelling radius of the single doors reduces the clearance between the separate enclosure suites and is ideally suited for restricted installation sites.

Material: Sheet steel

Colour: RAL 7035

Dimensions: enclosure (W x H): W: 800 mm H: 2000 mm