

**Rittal – The System.**

Faster – better – everywhere.



**DK 7825.366**

**Gland plate modules, vented, with  
airflow regulator**

State: 18/03/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7825.366 - Gland plate modules, vented, with airflow regulator for DK-TS

Gland plate modules, vented, with airflow regulator allow controlled air routing from the twin base to the installed components.



## Features

|                     |  |
|---------------------|--|
| Model No.           | DK 7825.366  |
| Product description | Allows controlled air routing from the twin base to the installed components. Individually adjustable membranes allow control of the air inlet opening between 10% and 80% free space. If the rear area of the enclosure is partitioned by base/gland plates, the required volumetric airflow may be individually regulated, and distribution of the airflow inside the twin base adapted to suit the requirements of each enclosure. The gland plate module may be combined with all gland plates as required. Gland plate module including contacting assembly screws, the additional installation of PE conductors is not required. |
| Material            | Sheet steel  |
| Supply includes     | Gland plate modules, vented<br>Filter mat<br>Assembly parts  |
| To fit              | Enclosure type: TS 8<br>Width: 600 mm  |
| Packs of            | 1 pc(s).   |
| Net weight          | 2.209 kg   |
| Gross weight        | 2.409 kg   |

# Features

---

|                       |          |
|-----------------------|----------|
| Customs tariff number | 94039910 |
| ECLASS 8.0            | 27189261 |

---

## Tender text

TS 8 / FR(i) gland plate module

For use in the base frame of the enclosure frame.

Module depth 238 mm, can be exchanged for gland plate module of the same dimensions.

Gland plate module can be used in enclosures of depth 600, 800, 900, 1,000 and 1,200 mm.

The gland plate module has several ventilation lamellas which can be set individually and thus allow the air to flow in in a target oriented way.

The air volume flow can also be regulated according to the degree of opening.

The ventilation opening can also be equipped with a filter mat if desired.

Material: Sheet steel

For enclosure width: 600 mm