

**Rittal – The System.**

Faster – better – everywhere.



**DK 7825.380**

**Gland plate modules, vented**

State: 16/05/2024 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7825.380 - Gland plate modules, vented for TS IT, TS, SE, TX CableNet

Gland plate modules, vented, for TS, TS IT, SE for use in the base frame of the network enclosure. Used in exchange for an existing gland plate of the same depth.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | DK 7825.380   |
| Product description   | Large perforated section for passive enclosure ventilation.                                   |
| Material              | Sheet steel   |
| Surface finish        | Zinc-plated   |
| Supply includes       | Filter mat and nylon tape   |
| Note                  | Several gland module plates need to be combined to close off the base completely in the TS-IT |
| Dimensions            | Depth: 237.5 mm   |
| To fit                | Enclosure type: TS<br>TS IT<br>SE<br>TX CableNet<br>Width: 800 mm                             |
| Packs of              | 1 pc(s).  |
| Weight/pack           | 2.15 kg   |
| Customs tariff number | 94039910  |
| EAN                   | 4028177233348   |
| ETIM 7.0              | EC002620  |
| ECLASS 8.0            | 27189261  |

## Tender text

Gland plate module, vented  
For W: 800 mm,  
Depth: 237,5 mm  
For TS, TS IT, SE, TX CableNet  
For cable entry with brush  
Sheet steel, vented