

Rittal – The System.

Faster – better – everywhere.



TE 7996.888

Network rack TE 8000

State: 20/06/2025 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7996.888 - Network rack TE 8000

TE 8000 IT enclosure with glazed door, prepared for individual interior installation.

Features

Model No.	TE 7996.888
Design	with side panels
Benefits	No frame structure Optimum accessibility Readily dismantled and therefore easily installed Interchangeable door hinge
Material	Sheet steel Glazed door: Single-pane safety glass, 3 mm
Surface finish	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
General colour	RAL 7035
Colour	RAL 7035
Supply includes	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Glazed door at the front, including 130° hinge, designer handle and security lock 3524 E Sheet steel door at the rear, including 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional population with module plates) Roof plate including concealed cut-out for cable entry and optional fan 4 levelling feet, M10 (supplied loose) 4 spacers, 20 mm (supplied loose) to raise the roof plate Side panels, lockable, including security lock 3524 E
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 1,000 mm
Units	42 U

Features

Units	42 U
Free mounting space to the 482.6 mm (19") level, front/rear	80 mm / 130 mm
Distance between levels as delivered	745 mm
Load capacity	4,000 N
Protection category to IEC 60 529	IP 20
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	126
Gross weight	132
EAN	4028177816725
ETIM 9	EC002499
ECLASS 8.0	27180207