

# Rittal – The System.

Faster – better – everywhere.



## DK 7161.000 Telescopic slides

State: 9/09/2025 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7161.000 - Telescopic slides for component shelves, for mounting on the VX enclosure frame and for upgrading existing VX and TS applications

For retrospectively converting fixed component shelves to full withdrawal by exchanging the fastening bolts or mounting rails (heavy-duty version) for the telescopic slides.

## Features

Model No.	DK 7161.000
Product description	Fixed component shelves are easily converted to full withdrawal. For this purpose, the existing fastening bolts or mounting rails (heavy-duty version) are exchanged for the telescopic slides.
Material	Sheet steel
Surface finish	Zinc-plated
Suitable for component shelf depth	600 mm
Load capacity	50 kg
Note	For installation and locking on a 25 mm pitch pattern in the enclosure depth.
Packs of	2 pc(s).
Net weight	2.16
Gross weight	2.34
PCF per pack (cradle-to-gate)	9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177126039
ETIM 9	EC002620
ECLASS 8.0	27189261

# Tender text

Telescopic slides for 600 mm deep base unit

The telescopic are installed inbetween the installation kit and the 600 mm deep component shelf.

The telescopic slides can hold a load up to a maximum of 50 kg and have double locks.

Material: Sheet steel, zinc-plated, passivated

For use with component shelf depths of: 600 mm