

# Rittal – The System.

Faster – better – everywhere.



## VX 8620.051

Base/plinth corner piece with base/  
plinth trim panels, front and rear,  
100 mm, stainless steel

State: 9/08/2025 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8620.051 - Base/plinth corner piece with base/plinth trim panels, front and rear, 100 mm, stainless steel for VX, TS, VX SE

Base/plinth corner pieces with moulded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point may be concealed with a corner and baying cover.

## Features

|                     |  |
|---------------------|--|
| Model No.           | VX 8620.051  |
| Product description | Base/plinth corner pieces with moulded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point may be concealed with a corner and baying cover.       |
| Material            | Base/plinth corner piece: Stainless steel 1.4301 (AISI 304)<br>Base/plinth trim panel front/rear: Stainless steel 1.4301 (AISI 304)<br>Corner and baying cover: Plastic  |
| Surface finish      | Trim panel: Brushed, grain size 400  |
| Supply includes     | 4 base/plinth corner pieces<br>4 corner covers<br>1 baying cover<br>2 base/plinth trim panels, front/rear, 100 mm high<br>Assembly parts   |
| Note                | Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth<br>Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system |
| Dimensions          | Height: 100 mm   |
| To fit              | Width: = 800 mm  |

# Features

|                       |   |
|-----------------------|---|
| Type rating to UL 50E | Type 1<br>Type 3R<br>Type 4<br>Type 4X<br>Type 12 |
| Weight/pack           | 6.5 kg  |
| Packs of              | 2 pc(s).  |
| Net weight            | 4.78  |
| Gross weight          | 4.86  |
| Customs tariff number | 94039910  |
| EAN                   | 4028177922303                                     |
| ETIM 9                | EC000721  |
| ECLASS 8.0            | 27182003  |

# Approvals

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|