


Rittal – The System.

Faster – better – everywhere.



SV 9340.004 Busbar support

State: 12/09/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.004 - Busbar support for flat copper busbars

For flat copper bars up to 800 A.

Features

Model No.	SV 9340.004
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Rated operating voltage	1000 V, 3~
Electrical ratings UL (SCCR)	22 kA - 600 V, support spacing 500 mm, 15 x 5 - 25 x 10 mm busbars 25 kA - 600 V, support spacing 500 mm, 30 x 5/10 mm busbars 30 kA - 600 V, support spacing 250 mm, 15 x 5 - 25 x 10 mm busbars 65 kA - 600 V, support spacing 250 mm, 15 x 5 - 25 x 10 mm busbars, Fuse Class L max. 800 A, JDDZ/7
Note on Model No.	If 12 x 5/10 mm busbars are used, spacer 9340.090 is additionally required The use of a base tray is required for UL applications UL approval only applies in conjunction with AC application
Number of poles	4-pole
Internal attachment	Yes
Centre-to-centre spacing of busbars	60 mm
To fit busbars	12 x 5 - 30 x 10
Packs of	4 pc(s).
Net weight	0.84
Gross weight	0.915
Customs tariff number	85469010
EAN	4028177536715

Features

ETIM 9	EC001166
ECLASS 8.0	27400607

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK