

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.400 OM adaptors

State: 18/11/2025 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.400 - OM adaptors with connection cables



## Features

|   |   |
|---|---|
| Model No.                                     | SV 9340.400   |
| Design  | With connection cable   |
| Material                                      | Polyamide<br>Fire protection corresponding to UL 94-V0  |
| Colour  | Chassis: RAL 7035   |
| Connection cables (AWG)                       | AWG 12  |
| Rated current max.                            | 25 A  |
| Rated operating voltage                       | 690 V, 3~   |
| Electrical ratings UL (SCCR)                  | 30 kA - 600 V, Fuse Class K5 max. 60 A, JDDZ/7<br>50 kA - 600 V, Fuse Class K5 max. 35 A, JDDZ/7<br>65 kA - 600 V, Fuse Class J max. 30 A, JDDZ/7<br>65 kA - 600 V, Fuse Class K5 max. 30 A, JDDZ/7<br>50 kA - 480 V, Combination Motor Controller max. 27 A, NKJH/7<br>65 kA - 480 V, Combination Motor Controller max. 32 A, NKJH/7 |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Length of connection cable                    | 130 mm  |
| Support rail type                             | Support frame, 1 x TS 45D, 2 x TS 45D-V   |
| Note  | The technical data may vary for UL applications   |
| Number of poles                               | 3-pole  |

# Features

---

|                              |                                |
|------------------------------|--------------------------------|
| Dimensions                   | Width: 90 mm<br>Height: 208 mm |
| Support rails Qty/height     | 3 / 10 mm                      |
| To fit busbars               | Height: 5, 10 mm               |
| Support frame (W x H)        | 45 mm x 170 mm                 |
| Packs of                     | 1 pc(s).                       |
| Net weight                   | 0.47                           |
| Gross weight                 | 0.473                          |
| Copper weight (kg per piece) | 0.036                          |
| Customs tariff number        | 85369095                       |
| EAN                          | 4028177673830                  |
| ETIM 9                       | EC001531                       |
| ECLASS 8.0                   | 27370304                       |

# Approvals

---

|              |  |
|--------------|--|
| Approvals    | ABS<br>DNV-GL<br>Lloyds Register of Shipping<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK          |