Rittal – The System.

Faster – better – everywhere.





SV 9340.950 Bus-mounting fuse base D-Switch

State: 16/10/2025 (Source: rittal.com/nz-en)



SV 9340.950 - Bus-mounting fuse base D-Switch

With integral visual fuse monitoring via flashing indicator and operating status display.

Features

Model No.	SV 9340.950		
Material	Polyamide Fire protection corresponding to UL 94-V0		
Colour	Chassis: RAL 7035 Fuse holder: RAL 7001		
Supply includes	Retaining springs for D 01 and 10 x 38 mm fuses		
Note	Wire end ferrules should be used with fine wire conductors		
For bar systems with centre-to- centre spacing	60 mm		
Type of electrical connection	Box terminal		
Fuse inserts	D 01 (with reducer) D 02 (with Neozed adaptor sleeve) 10 x 38 (with retaining spring)		
Fuse inserts footnote	When using D 01 and 10 x 38 mm fuses, reducers must be used. Use of D 01 fuses optionally possible with adaptor sleeve for D 0 base/plinths.		
Rated operating current max.	63 A		
Rated operating voltage	400 V, 3~		
Note	For the use of fuse inserts to EN 60 269-3 (DIN VDE 0636-3) With integral visual fuse monitoring via flashing indicator and operating status display as well as cable routing for conductors to 6 mm ²		
Test specification	IEC/DIN EN 60 947-3		
Dimensions	Width: 27 mm Height: 226 mm		
Connection of round conductors	1.5 - 25 mm²		

© Rittal 2025

Features

To fit busbars	Height: 5, 10 mm
Voltage range for indicator lights	100 - 400 V
Number of poles	3-pole
Packs of	3 pc(s).
Net weight	0.975
Gross weight	1.04
Copper weight (kg per piece)	0.066
Customs tariff number	85369095
EAN	4028177603400
ETIM 9	EC001046
ECLASS 8.0	27371402

Approvals

|--|--|--|

© Rittal 2025 3