

Rittal – The System.

Faster – better – everywhere.



SV 9344.110

NH fuse-switch disconnecter

State: 30/08/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.110 - NH fuse-switch disconnecter

Features

| | |
|---|---|
| Model No. | SV 9344.110 |
| Material | Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated |
| Colour | Chassis: RAL 7035 Cover: RAL 7035/7001 |
| Clamping area for laminated copper bars | Clamping area width: 32 mm Clamping area height: 10 mm |
| for mounting plate assembly | Yes |
| Cable outlet | Top/bottom |
| Type of electrical connection | Screw M10 |
| Rated operating current max. | 250 A |
| Rated operating voltage | 690 V, 3~ |
| For NH size | 1 |
| Note | The technical data may vary for UR applications. Applications to UR only in conjunction with "Special Purpose Fuses". |
| Test specification | IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts) |
| Dimensions | Width: 184 mm Height: 298 mm |
| Connection of round conductors | 10 - 150 mm ² |
| Number of poles | 3-pole |
| Packs of | 1 pc(s). |
| Net weight | 2.138 |
| Gross weight | 2.14 |
| Copper weight (kg per piece) | 0.3 |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 85365080 |
| EAN | 4028177540606 |
| ETIM 9 | EC000249 |
| ECLASS 8.0 | 27371401 |

Approvals

| | |
|--------------|---|
| Approvals | C-UR CQC-CCC UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |