

Rittal – The System.

Faster – better – everywhere.



KEL 9301.000 Ex enclosures

State: 14/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KEL 9301.000 - Ex enclosures stainless steel, empty enclosure with screw-fastened cover

Ex enclosure with screw-fastened cover, stainless steel



Features

| | |
|-----------------|---|
| Model No. | KEL 9301.000 |
| Design | Ex enclosures |
| Applications | Zone 1 and 2 or 21 and 22 to 2014/34/EC Ambient temperature range: -30 °C...+80 °C The specified temperatures may be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection thanks to increased safety (Ex e), equipment protection thanks to enclosure (Ex tb) |
| Material | Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal |
| Surface finish | Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm |
| Supply includes | Enclosure Cover |
| Dimensions | Width: 150 mm Height: 150 mm Depth: 80 mm |

Features

| | |
|-------------------------------------|---|
| Certificate IEC EX PTB 09.0033U | Yes |
| Certificate PTB 03 ATEX 1013U | Yes |
| Basic material | Stainless steel 1.4301 (AISI 304) |
| IP protection category to IEC 60529 | IP 66 |
| Packs of | 1 pc(s). |
| Net weight | 1.2 kg |
| Gross weight | 1.448 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002503 |
| ECLASS 8.0 | 27180502 |
| Product description | KEL Ex enclosure, WHD: 150x150x80 mm, Stainless steel 1.4301, without mounting plate, Empty enclosure with screw-fastened cover |

Approvals

| | |
|--------------|--|
| Approvals | ATEX ATEX QA CQC-CCC IECEX IECEX QAR |
| Explanations | Attestation of Conformity |