


Rittal – The System.

Faster – better – everywhere.



KEL 9302.000 Ex enclosures

State: 14/09/2025 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KEL 9302.000 - Ex enclosures Stainless steel, empty enclosure with screw fastened cover

Ex enclosure with screw-fastened cover, stainless steel



Features

Model No.	KEL 9302.000
Design	Ex enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EC Ambient temperature range: -30 °C...+80 °C The specified temperatures may be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection thanks to increased safety (Ex e), equipment protection thanks to enclosure (Ex tb)
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Enclosure Cover
Dimensions	Width: 300 mm Height: 150 mm Depth: 80 mm

Features

Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Basic material	Stainless steel 1.4301 (AISI 304)
IP protection category to IEC 60529	IP 66
Packs of	1 pc(s).
Net weight	1.94
Gross weight	2
Customs tariff number	94032080
EAN	4028177138568
ETIM 9	EC002503
ECLASS 8.0	27180502

Approvals

Approvals	ATEX IEC Ex
Explanations	Manufacturer's declaration