

**Rittal – The System.**

Faster – better – everywhere.



SV 9340.270  
OM supports

State: 17/01/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))



FRIEDHELM LOH GROUP

# SV 9340.270 - OM supports without contact system

For mounting of switchgear with external power supply.

## Features

Model No.	SV 9340.270
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
For bar systems with centre-to-centre spacing	60 mm
Support rail type	Support frame, 1 x TS 55D-V
Number of poles	3-pole
Support frame support	Yes
Dimensions	Width: 55 mm Height: 272 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	55 mm x 237 mm
Approvals	UL
Packs of	1 pc(s).
Net weight	0.25
Gross weight	0.258
Customs tariff number	85369095
EAN	4028177502475
ETIM 9	EC001166
ECLASS 8.0	27400607

# Approvals

---

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

---

## Tender text

OM support (without contact system)  
OM support without contact system (3-pole)  
for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Construction width: 55 mm

Length: 272 mm

Support frame: 55 x 237 mm

Support frame support: yes

PinBlock: -

Support rail: 1

System:

Rittal RiLine60