


Rittal – The System.

Faster – better – everywhere.



SV 9340.510 OM adaptors

State: 13/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.510 - OM adaptors with spring terminals



Features

| | |
|---|--|
| Model No. | SV 9340.510 |
| Design | with spring terminals |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | Chassis: RAL 7035 |
| Rated current max. | 32 A |
| Rated operating voltage | 690 V, 3~ |
| For bar systems with centre-to-centre spacing | 60 mm |
| Support rail type | without support frame, 1 x TS 45C |
| Number of poles | 3-pole |
| Dimensions | Width: 45 mm Height: 208 mm |
| Connection of round conductors | 1.5 - 6 mm ² |
| Support rails Qty/height | 1 / 10 mm |
| To fit busbars | Height: 5, 10 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.231 kg |
| Gross weight | 0.24 kg |

Features

| | |
|------------------------------|--|
| Copper weight (kg per piece) | 0.027 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV OM adaptor, 32 A, 690 V, 3-pole, tension spring clamp 1,5-6 mm ² , WH: 45x208 mm, support rail TS 45C |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV Lloyds Register |
| Explanations | Declaration of conformity Declaration of conformity UK |

Tender text

OM adaptor 32 A
OM adaptor 32 A with tension spring clamp, 3-pole,
for busbar thickness 5/10 mm and PLS 800/1600
Technical specifications
Construction width: 45 mm
Length: 208 mm
Support frame: -
Support frame support: -
PinBlock: -
Connector outlet: -
Support rail: 1 with anti-slip guard
System:
Rittal RiLine60