

Rittal – The System.

Faster – better – everywhere.



SV 9342.504

Circuit-breaker component adaptor

State: 12/04/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9342.504 - Circuit-breaker component adaptor 4-pole

Features

| | |
|---|--|
| Model No. | SV 9342.504 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Supply includes | Terminal cover Sliding blocks |
| Type of electrical connection | Box terminal |
| Rated current max. | 160 A |
| Rated operating voltage | 690 V, 4~ |
| Electrical ratings UL (SCCR) | 65 kA - 480 V, circuit breaker max. 125 A, DIVQ/7 |
| Cable outlet | Top |
| For bar systems with centre-to-centre spacing | 60 mm |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications |
| Number of poles | 4-pole |
| Dimensions | Width: 120 mm Height: 277 mm |
| Connection of round conductors | 35 - 120 mm ² |
| To fit busbars | Height: 5, 10 mm |
| Clamping area for laminated copper bars (W x H) | 18.5 x 15.5 mm |
| To fit manufacturer (model) | ABB (T1, T2, XT1, XT2) Eaton (NZM1-4/125 A, BZM E1-4/100 A) Schneider Electric (NSC100) Schrack (MC1) Siemens (3VA10, 3VA11) |

Features

| | |
|------------------------------|--|
| Approvals | UL |
| Packs of | 1 pc(s). |
| Net weight | 1.225 kg |
| Gross weight | 1.425 kg |
| Copper weight (kg per piece) | 0.258 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Circuit-breaker component adaptor, 160 A, 690 V, 4-pole, cable outlet top, round conductor connection 35-120 mm ² , clamping area WH: 18,5x15,5 mm |

Approvals

| | |
|--------------|---|
| Approvals | ABS Lloyds Register of Shipping UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |