

# Rittal – The System.

Faster – better – everywhere.



## SV 9343.130

## NH fuse-switch disconnector

State: 7/02/2026 (Source: [ittal.com/nz-en](http://ittal.com/nz-en))



FRIEDHELM LOH GROUP

# SV 9343.130 - NH fuse-switch disconnector with electronic fuse monitoring

## Features

Model No.	SV 9343.130
Design	For 60 mm busbar systems with electronic fuse monitoring
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 32 mm Clamping area height: 10 mm
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
Rated operating current max.	250 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	1
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 184 mm Height: 298 mm
Connection of round conductors	10 - 150 mm <sup>2</sup>
To fit busbars	Height: 5, 10 mm
Number of poles	3-pole
with electronic fuse monitoring	Yes

## Features

Round conductor cross-section	10 - 150 mm <sup>2</sup>
Packs of	1 pc(s).
Net weight	2.498
Gross weight	2.505
Copper weight (kg per piece)	0.44
Customs tariff number	85369095
EAN	4028177540354
ETIM 9	EC000249
ECLASS 8.0	27371401

## Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK