

Rittal – The System.

Faster – better – everywhere.



SV 9343.300

NH fuse-switch disconnecter

State: 21/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9343.300 - NH fuse-switch disconnecter

Features

Model No.	SV 9343.300
Design	For 60 mm busbar systems
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 32 mm Clamping area height: 10 mm
Note	Connection of sector-shaped conductors 120 – 300 mm ² .
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Box terminal
Rated operating current max.	630 A
Rated operating voltage	690 V, 3~
For NH size	3
Note	The technical data may vary for UR applications. Applications to UR only in conjunction with "Special Purpose Fuses".
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 250 mm Height: 298 mm
Connection of round conductors	95 - 300 mm ²
To fit busbars	Height: 5, 10 mm

Features

Clamping area for laminated copper bars	20 mm
Number of poles	3-pole
Round conductor cross-section	95 - 300 mm ²
Packs of	1 pc(s).
Net weight	4.48 kg
Gross weight	4.5 kg
Copper weight (kg per piece)	1.44
Customs tariff number	85369095
ETIM 9	EC000249
ECLASS 8.0	27371401
Product description	SV NH fuse-switch disconnecter, size 3, 630 A, 690 V, 3-pole, box terminal

Approvals

Approvals	C-UR CQC-CCC UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK