

Rittal – The System.

Faster – better – everywhere.



SV 9690.030 Energy storage frame

State: 15/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9690.030 - Energy storage frame VX ESS

Enclosure frame with roof plate and flexible interior fit-out. Ideal for efficient and modular energy storage installation.

Features

Model No.	SV 9690.030
Material	Enclosure frame: Sheet steel, 1.5 mm Mounting angles: Sheet steel, 2 mm Cross-member with mounting angle: Sheet steel, 3 mm
Surface finish	Enclosure frame: Dipcoat-primed Mounting angles: Zinc-plated Cross-member with mounting bracket: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure frame
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 600 mm
Packs of	1 pc(s).
Net weight	42 kg
Gross weight	42.5 kg
PCF per pack (cradle-to-gate)	106.89 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
ETIM 9	EC000261
Product description	VX ESS energy storage frame WxHxD: 600x2000x600 mm, with interior fit-out