

Rittal – The System.

Faster – better – everywhere.



SV 9344.330

NH fuse-switch disconnector

State: 20/01/2026 (Source: rittal.com/nz-en)



FRIEDHELM LOH GROUP

SV 9344.330 - NH fuse-switch disconnector with electronic fuse monitoring

Features

Model No.	SV 9344.330
Design	For mounting plate assembly with electronic fuse monitoring
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars for mounting plate assembly	Clamping area width: 50 mm Clamping area height: 10 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
Rated operating current max.	630 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	3
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 250 mm Height: 298 mm
Connection of round conductors	10 - 300 mm ²
Number of poles with electronic fuse monitoring	3-pole
Round conductor cross-section	10 - 300 mm ²

Features

Packs of	1 pc(s).
Net weight	4.4
Gross weight	4.444
Copper weight (kg per piece)	1.06
Customs tariff number	85369095
EAN	4028177542051
ETIM 9	EC000249
ECLASS 8.0	27371401

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK
