

Rittal – The System.

Faster – better – everywhere.



RX 9360.600

RiLineX CB component adaptor

State: 9/09/2025 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.600 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.

Features

Model No.	RX 9360.600
Design	universal
Benefits	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005 RAL 35745
Supply includes	3 connection space covers
IP protection category to IEC 60 529	IP 2XB
Rated impulse withstand voltage Uimp	12 kV
Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage	1,000 V
Overvoltage category	4
Contamination level	3
Number of poles	3-pole

Features

Cable outlet	Bottom
Type of electrical connection	Box terminal
To fit manufacturer (model)	ABB (A1, S2, T1, T2, XT1, XT2, FD63/FD160) BTicino (M1 160) Chint (NM8N-125, NM1-63H, NM1-125H, NXM-63S, NXM-125S, NXM-160S, NXMS-160) Eaton (NZM1) Fuji Electric (BW125JAG-3P) Hager (P160) Himel (HDM3-100F/N, HDM3L-125) Hyundai Electric (100AF, 125AF, 125D, 160D AF) Legrand (DPX 160, DPX 250 ER, DPX ³ 160) LS Electric (100AF, 125AF, TE100, TD100, TE160, TD160) Mitsubishi (NF63-SV, NF125-SV) OEZ (BC160) Rockwell (140G-C2C3-D10, 140G-C2C3-D12, 140-C2E3-D16, 140G-H0F3-D10, 140G-H0F3-D12, 140G-H0F3-D16) Sassin (3SM8L-100) Schneider (NSC100N, NSXm50, NSXm100, NSXm160, NSXm250, NSE100) Schrack (MC1) Siemens (3VA10, 3VA11) Terasaki (E125, S125)
To fit busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 81 mm Height: 252 mm Depth: 63 mm

Features

Packs of	1 pc(s).
Net weight	0.92
Gross weight	1.22
Copper weight (kg per piece)	0.375
Customs tariff number	85369095
EAN	4028177997103
ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------