## Rittal - The System.

Faster – better – everywhere.





# RX 9360.710 RiLineX component adaptor

State: 8/12/2025 (Source: rittal.com/nz-en)



## RX 9360.710 - RiLineX component adaptor

RiLineX component adaptor (16 A, 3-pole, including connection cables) in width 45 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.



#### **Features**

Model No.	RX 9360.710
Design	With connection cable
Benefits	For mounting equipment for top hat rail installation, e.g. motor
	starter
	Pre-assembled connection cable
	Simple clip locking for support rails
	Optional anti-slip guard
	Snap-on mounting and simple adjustment for busbar thickness
	(5/10 mm)
	Simple assembly
	Coordinated accessories reduce the number of different items
	required
Material	Polyamide (PA 6)
	Fire protection corresponding to UL 94
Colour	RAL 9005
	RAL 35745
Connection cables (AWG)	AWG 14
Rated current of round conductor	16 A
Rated current of round conductor (UL)	16 A

© Rittal 2025 2

### Features

Electrical ratings UL (SCCR)	5 kA - 600 V, RMS 100 kA - 600 V, Fuse Class RK5 max. 30 A, JDDZ/7 65 kA - 480 V, Combination Motor Controller max. 16 A, NKJH/7 30 kA - 600 V, Combination Motor Controller max. 12.5 A, NKJH/7 65 kA - 480 V, Combination Motor Controller max. 40 A, NKJH/7 50 kA - 480 V, circuit breaker max. 22 A, DIVQ/7
Cable outlet	Тор
For bar systems with centre-to- centre spacing	60 mm
Length of connection cable	150 mm
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 45 mm Height: 239.4 mm Depth: 36.2 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
IP protection category to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C55 °C
Storage temperature range	-25 °C75 °C

© Rittal 2025 3

## Features

Ambient humidity (non- condensing)	1090 %
Packs of	4 pc(s).
Net weight	1.2
Gross weight	1.35
Copper weight (kg per piece)	0.108
Customs tariff number	85369095
EAN	4028177997035
ETIM 9	EC001531

## **Approvals**

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025