

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.760

## RiLineX component adaptor

State: 4/07/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.760 - RiLineX component adaptor

RiLineX component adaptor (65 A, 3-pole, including connection cables) in width 54 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.



## Features

Model No.	RX 9360.760
Design	With connection cable
Benefits	For mounting equipment for top hat rail installation, e.g. motor starter Pre-assembled connection cable Simple clip locking for support rails Optional anti-slip guard Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Simple assembly Coordinated accessories reduce the number of different items required
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005 RAL 35745
Connection cables (AWG)	AWG 6
Rated current (max.)	65 A

# Features

Rated current of round conductor	65 A
Rated current of round conductor (UL)	65 A
Electrical ratings UL (SCCR)	100 kA - 600 V, Fuse Class RK5 max. 60 A, JDDZ/7 20 kA - 600 V, circuit breaker max. 60 A, DIVQ/7 65 kA - 480 V, Combination Motor Controller max. 52 A, NKJH/7
Cable outlet	Bottom
For bar systems with centre-to-centre spacing	60 mm
Length of connection cable	130 mm
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 54 mm Height: 239.4 mm Depth: 36.2 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
Rated impulse withstand voltage Uimp	8 kV
Rated insulation voltage Ui	1,000 V
IP protection category to IEC 60 529	IP 2XB
Maximum operating air humidity	90 %

# Features

Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Fire load	3.763 MJ/m <sup>2</sup>
Packs of	4 pc(s).
Net weight	1.84 kg
Gross weight	1.883 kg
Copper weight (kg per piece)	0.145
PCF per pack (cradle-to-gate)	13.53
Customs tariff number	85369095
ETIM 9	EC001531
Product description	RiLineX component adaptor (65 A, 3-pole, including connection cables) in width 54 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration

# Tender text

RiLineX component adaptor with mounting rail

Device adapters for mounting protective and switching devices for 60 mm busbar systems.

The device is mounted on a pre-assembled,

adjustable mounting rail.

For voltages up to 690 V AC and 690 V DC.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 65 A

Connection: 16 mm<sup>2</sup>

Cable outlet: top

Dimensions: 54 mm x 240 mm x 37 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360760