

# Rittal – The System.

Faster – better – everywhere.



## RX 9362.315

## RiLineX NH fuse-switch disconnecter

State: 7/09/2025 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9362.315 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 3 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M10 screw terminal connection. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.

## Features

|   |   |
|---|---|
| Model No.                                     | RX 9362.315   |
| Benefits                                      | Cover: can be locked and prepared for a lead seal<br>Voltage test through separate opening<br>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm<br>Tool-free changeover of the cable outlet<br>Park position for simpler maintenance work<br>High rated voltage 800 V ready<br>All variants also available with electronic fuse monitoring |
| Material                                      | Polyamide (PA 6)<br>Fire protection corresponding to UL 94<br>Contact tracks: Electrolytic copper, silver-plated  |
| Colour  | RAL 9005<br>RAL 35745   |
| Supply includes                               | Connectors for electronic fuse monitoring   |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Cable outlet                                  | Top/bottom  |
| Type of electrical connection                 | Screw M10   |
| Rated operating current max.                  | 630 A   |
| Rated operating voltage                       | 690 V AC  |
| For NH size                                   | 3   |
| Test specification                            | IEC/DIN EN 60 947-3<br>DIN EN 60 269-2 (fuse inserts)   |

# Features

|                                      |  |
|--------------------------------------|--|
| Dimensions                           | Width: 250 mm<br>Height: 349 mm<br>Depth: 135 mm |
| Operating temperature range          | -5 °C...35 °C                                    |
| Storage temperature range            | -25 °C...70 °C                                   |
| To fit busbars                       | 15 x 5/10<br>20 x 5/10<br>30 x 5/10              |
| To fit busbar system                 | RiLineX<br>RiLine60                              |
| Number of poles                      | 3-pole   |
| Contamination level                  | 3  |
| with electronic fuse monitoring      | Yes  |
| IP protection category to IEC 60 529 | IP 2XB   |
| Power dissipation (max.)             | 101 W  |
| Packs of                             | 1 pc(s).   |
| Net weight                           | 4.7  |
| Gross weight                         | 4.83   |
| Copper weight (kg per piece)         | 2.255  |
| Customs tariff number                | 85369095   |
| ETIM 9                               | EC001040   |

# Approvals

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|