

**Rittal – The System.**

Faster – better – everywhere.



**RX 9362.350**

**RiLineX NH fuse-switch  
disconnecter**

State: 3/04/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9362.350 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 3 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 120 to max. 300 mm<sup>2</sup>. Cable outlet can be at the top or bottom, as required.



## Features

Model No.	RX 9362.350
Design	For 60 mm busbar systems
Benefits	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring
Material	Polyamide (PA 6) Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	RAL 9005 RAL 35745
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Box terminal

# Features

Fuse inserts	NH 3
Rated operating voltage	690 V AC
For NH size	3
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 250 mm Height: 298.4 mm Depth: 134.9 mm
Operating temperature range	-5 °C...35 °C
Storage temperature range	-25 °C...70 °C
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
To fit busbar system	RiLineX RiLine60
Number of poles	3-pole
Contamination level	3
IP protection category to IEC 60 529	IP 2XB
Fire load	52.86 MJ/m <sup>2</sup>
Heat loss max.	101 W
Packs of	1 pc(s).
Net weight	4.7 kg
Gross weight	4.9 kg
Copper weight (kg per piece)	2.255
Customs tariff number	85369095
ETIM 9	EC001040

# Features

---

## Product description

RiLineX NH fuse-switch disconnecter in size 3 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 120 to max. 300 mm<sup>2</sup>. Cable outlet can be at the top or bottom, as required.

# Approvals

---

## Explanations

Declaration of conformity  
PCF-declaration

# Tender text

## RiLineX NH fuse-switch disconnecter (size 3)

NH fuse-switch disconnecter for  
60 mm busbar systems.

The device can be adjusted to rail thickness without tools.

Other properties include sealability,

Voltage test via separate openings,

Parking position for the cover and lockability with  
padlocks in the open position (service case).

Rated voltage 690 V AC.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm

Busbar dimensions: 5/10 mm

Rated current: 630 A

Type of electrical connection: Box terminal

Connection: 120 - 300 mm<sup>2</sup>

Cable outlet: top/bottom

Dimensions: 250 mm x 298 mm x 134 mm (BxHxT)

Manufacturer: Rittal GmbH & Co. KG  
Type: 9362350