Rittal - The System.

Faster – better – everywhere.





AX 1214.000 Basic enclosure AX, sheet steel

State: 29/11/2025 (Source: rittal.com/ro-ro)



AX 1214.000 - Basic enclosure AX, sheet steel

The compact enclosure AX with integral enclosure locators in the roof, base and side forms the familiar 25 mm system pitch pattern from the VX25 large enclosure. With this unique, patented system, AX compact enclosures are prepared for all types of configurations and refits. System components and accessories are easily, quickly and securely installed and retrofitted on rails, with no drilling required.







Features

Model No.	AX 1214.000
	AX 1214.000
Benefits	More interior installation options thanks to integral enclosure
	locators on a 25 mm system pitch pattern combined with the
	interior installation rail and our diverse range of system accessories
	Maintains the protection category (UL approval) by mounting the
	interior installation rail with no drilling required.
	Base configuration rail provides additional mounting level and
	increased load capacity
	Simple planning and configuration with the Rittal RiPanel
	configurator
Material	Enclosure: Sheet steel
	Door: Sheet steel, all-round foamed-in PU seal
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside,
	textured paint
	Mounting plate: Zinc-plated
Colour	RAL 7035

© Rittal 2025 2

Features

Supply includes	Enclosure with door(s) Gland plate(s) in enclosure base Mounting plate Perforated door strip Lock: 3 mm double-bit
Protection category NEMA	NEMA 1 NEMA 12
Protection category to IEC 60 529	IP 55
Type rating to UL 50E	Type 1 Type 12
IK Code	IK10
Dimensions	Width: 1,000 mm Height: 1,200 mm Depth: 400 mm
Material thickness - door	2 mm
Material thickness - enclosure	1,5 mm
Material thickness of mounting plate	2,5 mm
Dimensions mounting plate (W x H)	945 mm x 1,175 mm
Number of doors	2
Interchangeable door hinge	Yes
Lock	Lock version: 3-point lock system Number of locks: 1 Lock insert: 3 mm double-bit
Gland plate	Size: 6 Qty.: 2
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	82.1
_	

© Rittal 2025 3

Features

PCF per pack (cradle-to-gate)	265.7 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
EAN	4028177813090
E-Number Sweden	E3465164
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Certificates	Protection category
Explanations	Manufacturer's declaration
	Declaration of conformity
	Declaration of conformity UK
	PCF-declaration

Tender text

Enclosure (compact enclosure)

Enclosure with two doors:
Stable sheet steel construction
consisting of body folded from a single piece and welded,
with protection channel all-round door opening,
rear panel with eyelets for wall mounting bracket.

© Rittal 2025

Enclosure base with sheet steel gland plates.

Doors with foamed-in PU seal,

each door with vertical perforated door strip on both sides,

with PE conductor connection,

screw-fastened hinges.

130° opening angle to VDI (may be retrofitted to 180°),

locking rod with double-bit insert to DIN 43668

Mounting plate: With machined keyholes for earthing,

with imprinted scale, attached with ring nuts.

QR code:

QR code printed on body, cover and rating plate

for clear identification and easy retrieval of relevant

product information and documentation,

and for clear traceability of the individual parts.

Accessories: Comfort handle, lock inserts,

wall mounting bracket,

plastic and metal gland plates,

modular cable entry, earth straps,

wiring plan pockets, door stay, viewing window,

operating panels, fan-and-filter units, heaters,

swing frame, protective roof, 180° hinge

Material:

Enclosure, doors: Sheet steel

Mounting plate: Sheet steel, zinc-plated

Enclosure and door surface finish:

Triple surface treatment for optimum protection

against corrosion and resistance to mineral oils,

lubricants, machining emulsions and solvents:

Nanoceramic coating, electrophoretic dipcoat priming

Powder-coated on the outside in textured RAL 7035.

Protection category to IEC 60 529: IP 55

Protection category to UL 508A: Type 12

Dimensions (W x H x D): 1000 x 1200 x 400 mm

© Rittal 2025 5