

Rittal – The System.

Faster – better – everywhere.



PK 9500.050

Polycarbonate enclosures PK

State: 23/05/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9500.050 - Polycarbonate enclosures PK with knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

Model No.	PK 9500.050
Design	PK enclosure with solid cover
Material	Enclosure: Fibreglass-reinforced polycarbonate Cover: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08

Features

Dimensions	Width: 65 mm Height: 65 mm Depth: 57 mm
Cable entry (quantity x diameter)	M16/M20
No. of metric knockouts	4 x M16/M20
Operating temperature range	-35 °C...80 °C
Basic material	Polycarbonate
Packs of	12 pc(s).
Net weight	1.092
Gross weight	1.286
Customs tariff number	94037000
EAN	4028177490185
ETIM 9	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	C-UL UL
-----------	------------