Rittal – The System.

Faster - better - everywhere.





HD 2410.131 Cable gland HD

State: 04/11/2025 (Source: rittal.com/ro-ro)




HD 2410.131 - Cable gland HD

More compact design and the lock nut is included with the supply.







Features

| Model No. | HD 2410.131 |
|-----------------------------|---|
| Design | EMC |
| Benefits | Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with |
| | conventional cable glands. |
| Applications | Manufacturer |
| | Clean room technology (e.g. pharmaceuticals) |
| | Biotechnology |
| | Chemical industry |
| Material | Nut: Stainless steel 1.4305 (AISI 303) |
| | Seal: EPDM, compliant with FDA 21 CFR 177.2600 |
| Supply includes | Lock nut |
| Dimensions | Thread: M25 x 1.5 |
| For cable diameters | 12 - 17 mm |
| Operating temperature range | -20 °C100 °C |
| | |

© Rittal 2025

Features

| IP69 / IPX8 (5 bar, 30 min) |
|-----------------------------|
| Type 1 |
| Type 2 |
| Type 4 |
| Type 4X |
| Type 12 |
| Type 12K |
| Type 13 |
| 5 pc(s). |
| 0.54 |
| 0.59 |
| 73072980 |
| 4028177928664 |
| EC000441 |
| EC000441 |
| 27149109 |
| |

Approvals

| Approvals | UL + C-UL (listed) |
|-----------|--------------------|
| | VDE |

© Rittal 2025 3