


Rittal – The System.

Faster – better – everywhere.



SV 9676.748 Connection plate

State: 25/08/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.748 - Connection plate for laminated copper bars

For the connection of laminated flat copper bars.

Features

| | |
|---|---|
| Model No. | SV 9676.748 |
| Product description | For connecting laminated copper bars to a busbar distributor system made from flat copper. Suitable for 10 mm bar thickness. |
| Material | Connection plate: E-Cu Thrust piece: Stainless steel Busbar claw: Stainless steel |
| Supply includes | Assembly parts (excluding screws) |
| Assembly instruction | The required screw length must be selected in line with the busbar width W, i.e. length = W + fastening measurement. Screws are not included with the supply. Busbar claw with threaded insert M10 |
| Number of bars per conductor | 2 |
| Mounting dimensions | 50 mm |
| Clamping area for laminated copper bars (W x H) | 63 x 20 mm |
| To fit laminated copper bars | Qty.: 2 with no. of membranes: 10 with membrane width: 63 mm with membrane thickness: 1 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.47 |
| Gross weight | 0.478 |
| Copper weight (kg per piece) | 0.19 |
| Customs tariff number | 73269098 |
| EAN | 4028177625563 |
| ETIM 9 | EC002270 |

Features

| | |
|------------|----------|
| ECLASS 8.0 | 27400613 |
|------------|----------|

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|