

# Rittal – The System.

Faster – better – everywhere.



## SV 9682.152 Partial door

State: 22/06/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9682.152 - Partial door for VX

Door may be optionally hinged on the right or left.

## Features

Model No.	SV 9682.152
Product description	Suitable for VX enclosures instead of a door or rear panel. The partial doors may be combined with one another as required. A trim panel is required at the top and bottom in each case. Door may be optionally hinged on the right or left. In the case of doors without viewing panel (height 600 – 1000 mm), monitor frame 2305.000 may be installed. Standard double-bit lock insert may be exchanged for lock inserts, type A.
Material	Sheet steel, 2 mm
Surface finish	Textured paint
Colour	RAL 7035
Supply includes	Partial door Cross member Hinges Lock components Assembly parts
Note	Opening angle of partial doors max. 130°
Lock	Number of locks: 3
Dimensions	Width: 400 mm Height: 1,200 mm
To fit	Width: = 400 mm
IP protection category to IEC 60529	IP 54
Packs of	1 pc(s).
Net weight	9.1 kg
Gross weight	10.34 kg
PCF per pack (cradle-to-gate)	39.4 kg CO2 eq (Cat B)

# Features

---

Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204
Product description	VX Partial door, WH: 400x1200 mm sheet steel

# Approvals

---

Approvals	UL + C-UL (listed) UL + C-UL - FTTA
-----------	--