## Rittal – The System.

Faster – better – everywhere.





# SZ 2500.300 LED system light

State: 26/11/2025 (Source: rittal.com/ro-ro)



## SZ 2500.300 - LED system light

LED system light – the first light especially for enclosures! Highly innovative LED technology for even more light into the very last corner.





#### **Features**

Model No.	SZ 2500.300
Design	With motion detector
Benefits	Optimum illumination of the entire enclosure
	Optionally with clip, screw and magnetic attachment  A configuration to suit every application
Design	Motion sensor
	90° rotating connector
	Adjustable light direction
	Adjustable light distribution
Material	Light body: Extruded aluminium
	Light cover: Polycarbonate
	Light ends: PC-ABS
Colour	Enclosure: RAL 7016
Supply includes	Assembly screws
Power consumption	13 W
Connection options	Infeed, 3-pole
	Through-wiring, 3-pole
Motion detector	Yes

© Rittal 2025

### Features

Overvoltage category	II
Protection class	II (all-insulated)
Light – installation type	Screw-fastening Clip attachment Magnetic attachment (accessory)
Rated impulse withstand voltage, phase to earth	2500 V AC
Rated insulation voltage	300 V AC
Installation options	Directly onto the enclosure section with 25 mm pitch pattern
Luminous flux	1.200 lm
Light colour	4000 K (neutral white)
Note	Connection accessories should be ordered separately
Dimensions	Width: 437 mm Height: 85 mm Depth: 37 mm
Operating temperature range	-20 °C55 °C
Rated operating voltage	100 V - 230 V, 1∼, 50 Hz/60 Hz
IP protection category to IEC 60 529	IP 20
Packs of	1 pc(s).
Net weight	0.488
Gross weight	0.65
Customs tariff number	94054990
EAN	4028177809864
ETIM 9	EC000321
ETIM 8	EC000321
ECLASS 8.0	27189241

© Rittal 2025 3

## Approvals

Approvals	cqc-ccc
	ENEC
	UL
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 4