

# Rittal – The System.

Faster – better – everywhere.



## SV 9690.023

# Energy storage enclosure

State: 14/05/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9690.023 - Energy storage enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. Ideal for efficient and modular energy storage installation with component shelves.

## Features

Model No.	SV 9690.023
Design	Without interior fit-out
Material	Enclosure frame: Sheet steel, 1.5 mm Roof plate: Sheet steel, 1.5 mm Door: Sheet steel, 1.5 mm Rear panel: Sheet steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Powder-coated, textured paint
Colour	RAL 7035
Supply includes	Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit
Protection category to IEC 60 529	IP 20
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm
Packs of	1 pc(s).
Net weight	67 kg
Gross weight	67.7 kg
PCF per pack (cradle-to-gate)	221.54 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
ETIM 9	EC000261

# Features

---

Product description

VX ESS energy storage enclosure WxHxD: 800x2000x800 with door, rear panel

# Approvals

---

Explanations

Declaration of conformity